MAY/JUNE 2016

INDUSTRIAL LASER SOLUTIONS

FOR MANUEACTURING.

Joining polymers

Sub-surface marking

Introducing 2µm lasers

Cutting filter modules

Femtosecond processing

Graphene tailoring

Auto exhausts use laser processing



2µm lasers enable versatile

TRANSPARENT AND NONTRANSPARENT

PLASTICS ARE WELDABLE WITH HIGH

PRECISION AND EFFICIENCY

XIAONONG ZHU and SHIBIN JIANG



ver the last decade, significant progresses have been made in the development of various thulium-doped fiber lasers with a central wavelength near 2µm [1]. These newer 2µm fiber laser products range from 200W aver-

age power for continuous-wave (CW) operation [2] to 10kW peak power in pulsed mode operation [3, 4]. It is also possible for manufacturers to tailor the 2µm laser output performance according to specific application needs.


Much of the existing 1µm fiber laser technologies can be borrowed in constructing industrial-grade 2µm lasers. Many silica- and silica-fiber-based components commonly used in the visible and/or 1µm spectral regions may be also deployed in 2µm laser systems, except that their coatings are specified at different wavelengths.

Thus, the general performance of 2µm fiber lasers can be nearly as robust as their 1µm counterparts, especially in regard to compactness, efficiency, stability, and ease in daily operation, should their production be ramped up to meet any larger-scale potential applications.

Advantages of 2µm laser processing

Considering the vast amount of existing industrial applications for other wavelengths, why, when, and where would one need to consider 2µm lasers? The answer lies mostly in the absorption spectra of the materials to be processed [5]. For certain materials such as polymers where 1 or 0.8µm light is absorbed too little and 10µm or ultraviolet (UV) light is absorbed too much, 2µm may provide a new avenue of suitable light absorption. Some existing applications of UV to 1µm lasers can be also fulfilled with 2µm lasers, being much more eyesafe (retina-safe). Another wavelength-dependent aspect in laser material processing is beam focusability. At 2µm, these lasers represent a compromise between 1 and 10µm lasers in terms of minimum focusing spot diameter or pitch size for a given processing task.

Transmission spectra of COC, PC, PMMA, and clear ABS



Applications for 2µm lasers include transparent plastic welding [6, 7], embedded or multiple-layer marking of plastic panels, and precision thin polymer film welding and cutting. Note that for embedded marking, little or negligible damages on the front surface are possible. These unique applications FIGURE 1. Measured transmission spectra of four different transparent plastic samples, all with smooth or opticalgrade surfaces.

may not easily be implemented with other wavelength lasers.

"Transparent" means it is clear in the visible spectral range, but not necessarily transparent at other wavelengths. It happens that many plastic materials, intrinsically transparent in the visible, also have high transmission around 1µm, but not so at the wavelength near 2 µm. This is evident in the measured transmission spectra given in FIGURE 1 of four different types of transparent plastics: polymethylmethacrylate (PMMA), polycarbonate (PC), cyclic olefin copolymer (COC), and acrylonitrile butadiene styrene (ABS). From the spectral traces in FIGURE 1, it may be estimated that the respective absorption coefficient is at 2µm of 1.27/cm, 0.81/cm, 2.26/cm, and 1.38/cm for the four common plastic samples, whereas their corresponding absorption at 1µm is significantly less or negligible. Separate measurements of the transmission at the wavelength of 10µm for these samples, however, shows a transmission of less than 0.3%, corresponding to an estimated absorption coefficient of at least 58/cm or larger.

The spectral traces shown in FIGURE 1 also tell us that the absorption near 2µm is relatively flat, as the 2µm wavelength actually sits between two major absorption peaks—one around 1700 nm and another around 2150 nm. Based on the absorption coefficients derived from the transmission measurements for the four different transparent plastics, it may be deduced that at 2µm wavelength, with COC having highest absorption, it would be easier to weld compared with ABS, PMMA, and PC, whereas the PC sample with the lowest absorption per

processing of plastics

unit length would require significantly more power to weld. All of these are consistent with what we find in experiments.

Light absorption in plastic materials can be characterized into three basic categories: very strong absorption, very little absorption, and moderate absorption in between. The first category can cause effective surface heating, such as the majority cases where CO₂ lasers at 10µm or UV lasers are used. In contrast, the second category would often lead to no machining unless the laser power density is extremely high, such that the defects and/or the laser-enhanced defects become strongly absorptive and thus result in a sharp localized temperature rise followed by catastrophic ablation. The third category is where the 2µm laser light propagating inside polymers falls into. Here, light penetrates through the sample to a relatively longer distance, but in the meantime is attenuated because of absorption, thus heating up the sample.

In terms of effect on material processing, this third cate-

gory of absorption produces volume heating in general, and because of this it also provides the opportunity of marking at different layers for transparent or translucent plastics. In such cases, the front surface damage (or undesired deformation) at the beam entrance may be effectively reduced or even avoided through selecting appropriate numerical aperture of the focused laser beam and properly placing the workpieces in respect with the laser focus, plus the auxiliary means of surface cooling.

It should be added that not only the transparency, but sometimes also the darkness (or blackness) that appears in the visible spectral range, could be different at 2µm or another invisible wavelength. As demonstrated in FIGURE 2, laser welding of two pieces of PMMA plates—one clear (5.32mm thick) and one black (5.62mm thick)—can be achieved with the 2µm laser beam going through the black PMMA, rather than the other way around as we would usually expect. Actually, in this case, launching the laser from the clear piece fails to produce a solid bonding, which corresponds to the three shallow welding marks (one on the left and two on the right of the black welding track).

What is the explanation for this? The black is simply not black at 2µm! Using the same laser parameters and letting the 2µm beam enter from the clear PMMA, the corresponding maximum thickness of the clear PMMA

piece that may lead to a good weld or strong bonding is about 4.8mm. This is apparently inferior to that obtained by welding through the black piece.

Parameter windows for 2µm laser processing

For a given processing job, finding the best processing parameter windows with a $2\mu m$ laser is essentially the same as with other wavelength lasers. It normally includes trial and error in the selections of laser power or pulse energy, the laser beam diameter at the surface of workpiece, the scanning speed, and the relative movement pattern of the laser beam. With both pulse duration and pulse repetition rate often preset by laser manufacturers, the above-mentioned common variables represent the most important adjustable parameters for a laser processing engineer. This is no exception in using $2\mu m$ lasers.

For laser power selection, an optimized value should be sought between a minimum (threshold) and a maximum (overex-


posure). In some processing cases, a combination of either high power with greater beam moving speed or less power with lower speed (and longer processing time) would work. However, it may be more desirable to choose the high-power option so that the overall speed of processing can be increased as much as permissible, providing that the processing quality remains satisfactory.

Besides the laser power/pulse energy and the beam size at the processing site, the beam scanning speed directly affects the amount of effective laser dose at any given position for a given period of time. This is where the pulse repetition




FIGURE 2. Clear (top) and black (bottom) PMMA plates bonded together through the laser-produced welding track (the dark line slightly on the left of the sample). In this case, the CW 2µm laser beam actually entered the sample from the black piece, not from the clear piece.

a) 2µm CW laser-welded



Larger heat-affected zone

b) 2µm pulsed laser-welded



Small heat-affected zone

FIGURE 3. Cross-sections of the lap welds of 2.6mm transparent PMMA plates with CW (a) and pulsed (b) 2μ m lasers.

rate plays an important role. Once a beam scanning speed is chosen, higher repetition rate means greater spatial overlap between the laser-material interaction spots associated with any neighboring pulses, resulting in a higher effective number of pulses that strike at a given location.

Sometimes the basic question in welding is whether a pulsed or a CW laser should be used. FIGURE 3 shows a comparison between the cross-sections of PMMA welding with respective CW and pulsed 2µm lasers under a similar processing condition. It can be seen that for the pulsed laser welding result on the right, there is no observable front (top) surface damage and no gap present at the welding joint. But for the CW laser welding, noticeable top surface deformation and incomplete weld are present, along with a noticeably larger heat-affected zone (HAZ). Thus, it may be concluded that for precision transparent plastic welding, a pulsed 2µm laser with suitable specifications may be preferred, as it can lead to smaller welding

feature with lower average power and better quality of weld.

Examples of processing plastics

FIGURE 4 shows some thin transparent or translucent plastic samples processed with a commercially available 20 kHz, 180 ns, 2µm laser, which has a maximum average power of 10W. The dot separation of ~1.5 mm for spot welds in FIGURES 4A and 4B gives us an idea of the scales of these micro-welds. Normally, these welded parts cannot be peeled off easily unless damaging the samples. As shown by the laser-written "spot welding" in FIGURE 4b, the highly localized melt (and solidification thereafter) also provides an effective approach to marking these thin plastic materials. In other words, it is possible that both welding and marking may be achieved using the same 2µm pulsed laser for some transparent polymers.

Welding with a 2µm laser is by no means limited to only transparent or translucent thermoplastics. Colored or white plastic

and some thermo-elastic materials may be also bonded with sufficient strength by using 2µm laser light. The latter would have great potential in biomedical applications. Precision 2µm laser welding of thin polysulfone strings, polyvinyl chloride (PVC) tubes, IV bags, and polyurethane balloons have produced promising results, and FIGURES 4C through 4E show examples of laser-welded PVC tubes, a section of an IV bag, and an internal retention balloon. Besides the cosmetic aspects, all of these welding jobs require good seal for liquid under certain pressure.

Bonding of microchannel devices or biochips is another area incorporating 2µm lasers, and the interest in this application is increasing. Compared with the conventional hot plate bonding method, use of a 2µm laser to weld and seal microchannel devices-including all channel paths and their entry/exit ports-offers advantages in precision, energy efficiency, and flexibility, which should also help to significantly reduce the prototyping time. FIGURES 4F and



4G show the representative micro-welding tracks on a PMMA sample using a pulsed 2µm laser. The width of these thin welding lines can be readily controlled according

to the design of micro-channel devices. While the width of these welding lines can typically be between 0.3 and 0.5mm, even thinner welding tracks are possible.

FIGURE 5 shows the results of surface marking of a PC sample using a pulsed 2µm laser. As shown on the left, with different amounts of laser exposure, the




FIGURE 4. Examples of transparent/ translucent thin plastic films or sheets processed with a 2µm laser, including translucent 30µm-thick Nylon 66 on top of 90µm-thick Nylon 66 bonded together through lapped line welding and spot welding (a); 0.23mm-thick PC films lap welded together (b); laser-bonded PVC tubes, a section of an IV bag, and an internal retention balloon (c-e); a top view of typical welding tracks on a PMMA plate with curved welding lines (~400µm in width) to seal around the micro-channel entrance/exit and straight lines (180µm in width) to be placed besides microchannels (f, g); 0.25mm-thick transparent polyethylene terephthalate (PET) welded to a piece of 1.85mm-thick PMMA plate (h); and a microscopic image of a 40µm-diameter molten and re-solidified spot in PMMA (i).

Small is the new BIG

Newport Motion Solutions for Laser Micromachining Enable:

- Optimized Path Control
- Tight Focal Planarity
- Nanometer Scale Line Uniformity
- Trajectory-Based Laser
 Triggering











=100 c...

Newport Motion Solutions now include Solution Solution Controllers.


For more information call (800) 222-6440 or visit www.newport.com/micromachining-15



darkness of the laser-processed area can be gradually altered in a well-controlled manner. In particular, both black and clear marks (FIGURE 5, at right) may be achieved. It is worth mentioning that marking the transparent plastics with a 2µm laser can be based on two very different physical mechanisms, namely ablation and melting with re-solidification. For the latter, it is


possible that rise in temperature in the later process may cause these marks to disappear if the temperature reaches beyond the melting point of the chosen plastic material. In contrast, the ablation-generated marking would normally survive the aftermath of a period of enhanced heating. Nevertheless, the ablation-based marking, often accompanied with unwanted cracks and chips, is likely linked to some more severe structure damage to the material and this would also not be preferred. Therefore, a delicate marking scheme with nearly no damage to the surrounding area or with only minimal HAZ and, in the meantime, also survivable during severe heating needs to be sought at least for some specific applications. A special processing method has been successfully developed in our laboratory towards solving this issue.














FIGURE 5. Examples of marking a transparent PC plate to different darkness with a 30kHz, 30ns, 2µm laser include raster scanning (see left-side areas) of the focused laser beam with 4.6W (a), 5.9 W (b), 7.5 W (c), and 8.9 W (d) average power (rastering speed: 1000mm/s, line separation: 40µm, and three repeated scans for each case). (e) and (f) show the possibility of making either dark or clear marks on the same sample through laser parameter control. Each picture measures approximately 2.0×1.7 mm².

LASER MICROMACHINING

PhotoMachining, Inc. performs precision laser micromachining on a variety of different materials including plastics, metals, glass, ceramics, etc. Our eleven different types of lasers allow us wide flexibility to address many applications. We also design and manufacture custom laser machine tools.





PhotoMachining, Inc.

Contact sales@photomachining.com Tel: 603-882-9944

Web site: www.photomachining.com

CREATE BLACK ON METAL



6000 METAL MARKING SOLUTION

- CO₂ or Fiber Lasers
- Jet Black Color
- Outdoor/UV Stable
- NASA Tested
- Mil-Spec Compliant



www.LaserBits.com 800.733.7705

Subsurface marking of transparent plastics is achievable with a pulsed 2µm laser. This normally requires a good control of the laser beam focus position. FIGURE 6a shows an example of the embedded or subsurface marking in a 1mm-thick translucent polypropylene (PP) sample. In this case, both the front and the back surfaces of the sample are intact.

Fine cutting or drilling of plastics, fabrics, and various papers are also possible using pulsed 2µm lasers. FIGURES 6B and 6C show laser-cut/drilled 30µm-thick low-density

polyethylene (LDPE) film and a matrix of 50µm-diameter holes on 10µm-thick food wrap film.

To summarize, optical absorption of many plastic materials around the 2µm wavelength provides versatile and, in some cases, also unique opportunities for laser processing in this spectral region. Transparent and nontransparent plastic or elastomer materials without or with absorbing additives can be welded with high precision and efficiency using 2µm lasers. Subsurface/multilayer marking and cutting/drilling of thin plastic

films are possible by optimizing the 2μm laser processing parameters.


As more high-power and robust 2µm fiber lasers become commercially available, as well as their integrated systems, a variety of new applications and processing schemes may be developed around the 2µm spectral window, which in a broader sense may cover the less-explored 1.6–2.4µm spectral region in the entire existing laser material processing field. **

REFERENCES

- J. Geng and S. Jiang, "Fiber lasers: The 2 µm market heats up," Optics & Photonics News, 34–41 (Jul/Aug. 2014); see http://bit.ly/1S4qk3G.
- 2. See http://bit.ly/1S4o01p.
- 3. See http://bit.ly/1RUlqle.
- 4. See http://bit.ly/1RAsgVy.
- T. Hoult, "Understanding processing with thulium fiber lasers," Industrial Laser Solutions (Nov. 27, 2013); see http:// bit.ly/1XcZnPx.
- 6. See http://bit.ly/1M0v5SG.
- 7. See http://bit.ly/2013vUB.

XIAONONG ZHU (zhu@advaluephotnics.com) and SHIBIN JIANG (sjiang@advaluephotnics.com) are with AdValue Photonics, Tucson, AZ; www.advaluephotnics.com








FIGURE 6. Subsurface marking of a 1mm-thick translucent PP (a); laser-cut, 30μ m-thick LDPE thin films (b); and a micro-hole array drilled in a 10μ m-thick food wrap film (c), all using a 180ns, 20kHz, 2μ m laser.

CO₂ Laser Optics

Factory direct replacement optics for most industrial laser systems shipped within 24 hours

- Focusing Lenses Mirrors Output Couplers Featuring
- High Accuracy■ Low Absorption■ Made in USA■ Large Inventory

OEMs, CMs, distributors, and end-users, *contact us today* for the highest quality CO₂ Laser Optics delivered immediately from stock at extremely competitive prices.




Lens cleaning kit improves laser performance by removing spatter and blow-back.



ZnSe Optics meet OEM & ISO-10110 specifications and are suitable drop in field replacements for most popular lasers.



Mounting service into customer supplied focusing lens holders assures finished assembly will meet pressure requirements.





A Division of Meller Optics, Inc.

120 Corliss Street, Providence, RI 02904 (888) 239-5545 FAX (401) 331-4004 sales@laserresearch.net • www.laserresearch.net

ISO9001:2008 Certified